

# DATASHEET

## FFP MASKS

PROTECTION AGAINST DUST, MIST & FUMES



### SMART SERIES

#### FFP1 NR D



**2380** non valved



**2385** with Ventex®-valve

#### FFP2 NR D



**2480** non valved



**2485** with Ventex®-valve

#### FFP3 NR D




**2500** non valved



**2505** with Ventex®-valve

### CHARACTERISTICS



#### ActivForm®

Automatically fits to the face.  
No manual adjustments by the user are necessary.




#### DuraMesh®

Masks have a strong and durable structure.




#### Ventex®-valve

Starts to open even at low exhalation pressure and significantly reduces moisture and heat inside the mask.




#### Nose seal

The flexible nose seal improves fit and provides optimum wearing comfort.




#### Adjustable Strap

Makes it easier to take the mask on and off and to adjust to different head/neck dimensions.



#### Clip

Easy on & off; mask can be worn around the neck during breaks.



#### Dolomite clogging test

Masks have passed the Dolomite clogging test, giving the user better breathing resistance for longer.



#### 100% PVC-FREE

All Moldex products and packaging are completely free from PVC.

**NR (non reusable)** = Single use.  
Comfortable and durable throughout the whole shift

### CERTIFICATION

The Moldex Smart FFP-masks meet the requirements of EN149:2001 + A1:2009. The products are CE-marked in accordance with the requirements of EU regulation (EU)2016/425. The IFA (0121) in St. Augustin (Germany) is responsible for type examination (Module B) and monitoring of production (Module D). The products are manufactured in an ISO 9001 certified plant.

**Information for the UK market:** UKCA-marked in accordance with the requirements of PPE Regulation 2016/425 as brought into UK law and amended. Responsible for Module D surveillance: BSI-Assurance UK Ltd. (Identification number 0086), United Kingdom. UK Importer: Moldex/Metric AG & Co. KG · Unit 9, Glaisdale Point · Off Glaisdale Drive, Bilborough · Nottingham. NG8 4GP · Tel. +44 (0)115 985 4288 · info@uk.moldex-europe.com

### MATERIALS

**Filter Layer, Inner Shell, DuraMesh®:** Polypropylene, Ethylene-vinyl acetate (EVA)

**Nose Seal, Clip:** Polyethylene

**Ventex®-valve:** Natural Rubber

**Head Strap:** Polyester, Lycra

### WEIGHT

**2380:** 18 g **2385:** 18 g **2480:** 18 g **2485:** 17 g

**2500:** 17 g **2505:** 24 g

### AREAS OF USE

| Level | WEL  | Hazard type                                                                                                                 |
|-------|------|-----------------------------------------------------------------------------------------------------------------------------|
| FFP1  | 4x   | Fine dusts, fumes, water and oil based mists/aerosols                                                                       |
| FFP2  | 10 x | Hazardous fine dusts, water and oil based mists/aerosols, Biological agents of risk group 2                                 |
| FFP3  | 20 x | Harmful and carcinogenic dusts, water and oil based mists/aerosols, biological agents of risk group 2 and 3, CMR-substances |

(WEL = Workplace Exposure Limit)

# DATASHEET

## FFP MASKS

PROTECTION AGAINST DUST, MIST & FUMES



### TESTING ACCORDING TO EN 149:2001+A1:2009

#### Total inward leakage

Ten test subjects perform a variety of exercises. During the exercises the amount of test aerosol that penetrates the filter, face seal and valve are sampled. The total inward leakage of 8 out of 10 test subjects shall not exceed the following levels:

| Category | max. total inward leakage |
|----------|---------------------------|
| FFP1     | 22 %                      |
| FFP2     | 8 %                       |
| FFP3     | 2 %                       |

The filter penetration after loading the filter with 120 mg paraffin oil according to EN 149:2001 + A1:2009 shall not exceed the following levels:

| Category | max. Filter penetration |
|----------|-------------------------|
| FFP1     | 20 %                    |
| FFP2     | 6 %                     |
| FFP3     | 1 %                     |

#### Flammability

4 respirators are passed through a 800°C (+/- 50°C) flame with a speed of 6 cm/s. After passing through the flame the respirator has to self-extinguish.

#### Breathing Resistance


The breathing resistance produced by the filter of the respirator is tested at an airflow of 30 l/min and 95 l/min.

| Category | max. breathing resistance according to EN 149 |            |
|----------|-----------------------------------------------|------------|
|          | 30 l / min                                    | 95 l / min |
| FFP1     | 0,6 mbar                                      | 2,1 mbar   |
| FFP2     | 0,7 mbar                                      | 2,4 mbar   |
| FFP3     | 1,0 mbar                                      | 3,0 mbar   |

### INSTRUCTIONS FOR USE

- The user has to be trained and instructed in wearing the mask.
- FFP Masks do not protect against gases and vapours.
- The oxygen concentration of the ambient atmosphere should be at least 19,5 % Volume.
- These respirators may not be used if the concentration type, and properties of contaminants in the ambient atmosphere are unknown or at dangerous levels.
- Respirators should be disposed if damaged, if the breathing resistance becomes high due to clogging, or at the end of a shift.
- Never tamper with, alter or modify the respirator.

### INSTRUCTIONS FOR FITTING




1. Pull strap to form a large loop.



4. Adjust strap by pulling loop on strap.



2. Place respirator on chin and pull loop over head tight to the neck.



5. During breaks unclip strap.



3. Pull upper strap and place on back of head.



6. Let mask hang around your neck.

### INFO

For help on selection and training please contact us. We offer a wide range of training packages and support material.

MOLDEX/METRIC AG & Co. KG  
Unit 9, Glaisdale Point  
Off Glaisdale Drive, Bilborough  
Nottingham. NG8 4GP

Tel.: +44 (0)115 985 4288  
Fax: +44 (0)115 985 4211  
www.moldex-europe.com  
info@uk.moldex-europe.com